



Control and indication station, 2ПКП series.

Order table.

2ПКП	X	X	X	X	X	X	X	X	X	X	X
Double plastic station	Device 1 * (upper station)	Contacts	Color	Lamp 1 (upper station)	Color	Device 2 * (lower station)	Contacts	Color	Lamp 2 (lower station)	Color	Cable glands
2ПКП	see sheet 8-11	10	Зел	~380 V	Зел	see sheet 8-11	10	Зел	~380 V	Зел	1
		01	Кр	~220 V	Кр		01	Кр	~220 V	Кр	2
		11	Бел	=24 V	Бел		11	Бел	=24 V	Бел	3
		20	Син		Син		20	Син		Син	4
		02	Желт		Желт		02	Желт		Желт	
		21	Черн				21	Черн			
		12					12				
		22					22				
		30					30				
		03					03				
		31					31				
		13					13				
		40					40				
		04					04				

* the total number of contacts in each device cannot exceed four.

Specify 00 in the order number for unused elements.

Example: Station 2ПКП-3у230-00/ПДФ203ел-2203ел-2

Double station, with 230V buzzer; with two-position maintained selector switch (green) with two NO contacts, with a green 220V lamp; with two cable glands.

Text of inscriptions: 1 - "_____"; 2 - "_____"; 3 - "_____"; 4 - "_____".

The list of installed devices is on page 4/7.

Contact description	
10	1H0
01	1H3
11	1H0+1H3
20	2H0
02	2H3
21	2H0+1H3
12	1H0+2H3
22	2H0+2H3
30	3H0
03	3H3
31	3H0+1H3
13	1H3+3H0
40	4H0
04	4H3

NO - normally open contact

NC - normally closed contact

Supply with acceptance:

- RMRS

- RRR

