



Control and indication station, 3ПКП series.

Order table.

3ПКП	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X			
Triple plastic station	Device 1 * (upper station)			Lamp 1 (upper station)			Device 2 * (middle station)			Lamp 2 (middle station)			Device 3 * (lower station)			Lamp 3 (lower station)			Cable glands
	Designation	Contacts	Color	Voltage	Color	Designation	Contacts	Color	Voltage	Color	Designation	Contacts	Color	Voltage	Color				
3ПКП	see pp. 8–11	10	Зел	~380 V	Зел	see pp. 8–11	10	Зел	~380 V	Зел	see pp. 8–11	10	Зел	~380 V	Зел	1			
		01	Кр	~220 V	Кр		01	Кр	~220 V	Кр		01	Кр	~220 V	Кр	2			
		11	Бел	=24 V	Бел		11	Бел	=24 V	Бел		11	Бел	=24 V	Бел	3			
		20	Син		Син		20	Син		Син		20	Син		Син	4			
		02	Желт		Желт		02	Желт		Желт		02	Желт		Желт				
		21	Черн				21	Черн				21	Черн						
		12					12					12							
		22					22					22							
		30					30					30							
		03					03					03							
		31					31					31							
		13					13					13							
		40					40					40							
		04					04					04							

* the total number of contacts in each device cannot exceed four.

Specify 00 in the order number for unused elements.

Example: Station 3ПКП-КД11-00/КД11-2203ел/КА02-220Кр-2

Triple station, with double push-button with one NO and one NC contact;
with double push-button with one NO and one NC contact, with green 220V lamp;
with emergency stop push-button with two NC contacts, with red 220V lamp;
with two cable glands.

Text of inscriptions:

1 - "_____"; 2 - "_____"; 3 - "_____";
4 - "_____"; 5 - "_____"; 6 - "_____".

The list of installed devices is on page 4/7.

Contact description	
10	1H0
01	1H3
11	1H0+1H3
20	2H0
02	2H3
21	2H0+1H3
12	1H0+2H3
22	2H0+2H3
30	3H0
03	3H3
31	3H0+1H3
13	1H3+3H0
40	4H0
04	4H3

NO - normally open contact

NC - normally closed contact

Supply with acceptance:

- RMRS
- RRR

