



Control and indication station, ПКП series.

Order table.

ПКП	X	X	X	X	X	X
Plastic station	Device *			Lamp		Cable glands
	Designation	Contacts	Color	Voltage	Color	
ПКП	see sheet 8-11	10	Зел	~380 V	Зел	1
		01	Кр	~220 V	Кр	2
		11	Бел	~24 V	Бел	3
		20	Син		Син	4
		02	Желт		Желт	
		21	Черн			
		12				
		22				
		30				
		03				
		31				
		13				
		40				
		04				

Contact description

10	1H0
01	1H3
11	1H0+1H3
20	2H0
02	2H3
21	2H0+1H3
12	1H0+2H3
22	2H0+2H3
30	3H0
03	3H3
31	3H0+1H3
13	1H3+3H0
40	4H0
04	4H3

NO - normally open contact

NC - normally closed contact

* the total number of contacts in each device cannot exceed four.

Specify 00 in the order number for unused elements.

Example: Station ПКП-К320Кр-24Кр-2

Station with a red non-latching push-button protected against accidental actuation, with two NO contacts, with red 24V lamp, with two cable glands.

Text of inscriptions: 1 - "_____"; 2 - "_____".

The list of installed devices is on page 4/7.

Supply with acceptance:

- RMRS
- RRR

